



CURBY MINI-TAPER[™]

INTRODUCING THE CURBY MINI-TAPER

The Curby Mini-Taper is a sleek, lightweight manual water-activated tape dispenser with a small footprint. Weighing only 6 pounds, it is perfect for small office or home office, retail outlets and low-volume shipping environments with limited workspace. This dispenser is economically priced, easy to operate and the tape is simple to load. Paired with curbside recyclable water-activated tape, the Mini-Taper is part of IPG's line of "Curby" packaging solutions. The Curby Mini-Taper allows any size business to enjoy the carton sealing benefits of water-activated tape:

security, strength and professional packaging.

QUALITY, PRODUCTIVITY & PERFORMANCE

- Soft touch tape delivery
- Easy push tape dispensing
- Self-contained cutting mechanism delivers clean, even cutting of reinforced Kraft water-activated tape

INI-TAPER

S MINI-TAPER

- Better Pack water brushes provide consistent, uniform tape wetting
- Refillable and spill-resistant water tank holds enough water to activate one roll of tape
- Push lever dispenses 10" length of tape; repeat push lever for longer tape lengths

ENVIRONMENTALLY RESPONSIBLE

- Water-activated tape is recyclable and repulpable
- Only one strip of water-activated tape is needed for a secure, strong seal
- Portable dispenser does not require electricity



ipg) intertape polymer group

888-898-7834 | itape.com



800-237-9151 | betterpackages.com

SPECIFICATIONS

Model Number	BP222	
Dimensions	14.1" L x 8" W x 7.25" H (35.8 cm L x 20.3 cm W x 18.4 cm H)	
Shipping Weight	6 lbs. (2.72 kg)	
Maximum Roll Capacity	328 ft (100 m)	
Tape Width	70 mm	
Water Tank Capacity	8 fl. oz. (237 ml)	
Warranty	1 year parts and materials; 6 month labor	
Electrical Requirement	N/A	
Gum In/Gum Out	Gum In	

WAT SKU	Style	Size	Color	Reinforced
K9222HT	Venom	70mm x 100m	Natural	~
99298	Venom	70mm x 100m	Natural	~
99304	Venom	70mm x 100m	Natural	~
K5222HT	160	70mm x 100m	Natural	

EASY TO OPERATE



Eject and fill the water tank, then insert it back into place.

the second



Remove cover to insert tape, then feed tape through slot.



Push lever to dispense tape to desired length (Additional pushes may be required).



Push cutter down to cut the tape.





